



# Fluorescent Lamp Holders, Compact Type, 18-55 Watt 2G11, Horizontal Mount, Snap-In

By Bryant  
Catalog # [RL42G11HSM](#)

Fluorescent Lamp Holders, Compact Type, 18-55 Watt 2G11, Horizontal Mount, Snap-In



## Application

Compact Fluorescent

## General

Color	<ul style="list-style-type: none"> <li>• White</li> <li>• Blanc</li> </ul>
Item Type	Fluorescent Lampholders
Lamp Size	2-G11 Base 4) Pin
Material	Composite
Material - Mounting Hardware	Horizontal Screw Down
Performance	<ul style="list-style-type: none"> <li>• Electrical - Rating - 26-32W lamp type, 75W, 600V</li> <li>• Mechanical - Terminal Accommodation - Push-in wire terminals for #18 AWG solid or twist and tin stripped 7/16 inch wire</li> </ul>
Series	Lampholders
Type	Compact Fluorescent
UPC	883778303968

## Electrical Ratings

Connectivity	Screw Terminals
Current Rating	Telephone/CATV
Frequency Rating	60 Hz
Voltage Rating	600V AC kV

## Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> <li>• C/US UL Listed</li> <li>• CSA Certified</li> </ul>
----------------------	---

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

## Related Products

- [RL42G11H9 - Fluorescent Lamp Holders, Compact Type, 18-55 Watt 2G11, 90 Degree Horizontal Mount, Snap-In](#)
- [RL42G11HSM - Fluorescent Lamp Holders, Compact Type, 18-55 Watt 2G11, Horizontal Mount, Snap-In](#)
- [RL426G24 - Lampholder, Compact Fluorescent, 26- 32Watt, G24, Horizontal Screw In, White](#)



A proud member of the Hubbell Family.