



Fluorescent Lamp Holders, Compact Type, 18-55 Watt 2G11, Horizontal Mount, Snap-In

By Bryant
Catalog # [RL42G11HSM](#)

Fluorescent Lamp Holders, Compact Type, 18-55 Watt 2G11,
Horizontal Mount, Snap-In



Application

Compact Fluorescent

General

Color	<ul style="list-style-type: none">White
EU RoHS Indicator	No
Item Type	Fluorescent Lampholders
Lamp Size	2-G11 Base 4) Pin
Material	Composite
Material - Mounting Hardware	Horizontal Screw Down
Performance	<ul style="list-style-type: none">Electrical - Rating - 26-32W lamp type, 75W, 600VMechanical - Terminal Accommodation - Push-in wire terminals for #18 AWG solid or twist and tin stripped 7/16 inch wire
Series	Lampholders
Type	Compact Fluorescent
UPC	883778303968

Electrical Ratings

Connectivity	Screw Terminals
Current Rating	Telephone/CATV
Frequency Rating	60 Hz
Voltage Rating	600V AC kV

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">C/US UL ListedCSA Certified
----------------------	--

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - WDK BB-7 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Catalogs - Bryant Full Line Catalog](#)



A proud member of the Hubbell Family.