



# RECESS TR DUP RCPT, 15A 125V, IVORY

By Bryant  
Catalog # [RR1510I](#)

SNAPFIT TR Duplex Receptacle 15A



## Features

- Tamper-Resistant (TR) duplex
- Easily mounts to a one gang box
- Back and side wiring

## General

Color	<ul style="list-style-type: none"><li>• Ivory</li><li>• Ivoire</li></ul>
EU RoHS Indicator	Contact Manufacturer
Series	Special Use
Style	Clock Hanger / Recessed Receptacles
Type	Duplex Receptacle
UPC	883778305719

## Electrical Ratings

Current / Amperage Rating	15 A
Voltage Rating	125 V
Voltage Rating Description	125 V

## Logistics

Carton Quantity 10

## Product Assets

[Catalog Page - Bryant A-24 Catalog page](#)  
[Catalog Page - Bryant R-2 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)  
[Literature - Concealled Connections](#)  
[Literature - Home Entertainment](#)  
[Literature - Residential Catalog](#)

## Related Products

[RR1514I - RECES TR DUP RCPT 2G W/SNAPFIT,15A 125IV](#)  
[RR1512I - RECESS TR DUP RCPT 2G W/FEED,15A 125V,IV](#)  
[RR1510LA - RECESS TR DUP RCPT, 15A 125V, LG ALMOND](#)  
[RR1514LA - RECES TR DUP RCPT 2G W/SNAPFIT,15A 125LA](#)  
[RR1512LA - RECESS TR DUP RCPT 2G W/FEED,15A 125V,LA](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-RR1510I-SPEC-EN | REV 7/2023