



RECESS TR DUP RCPT, 15A 125V, LG ALMOND

By Bryant
Catalog # [RR1510LA](#)

SNAPFIT TR Duplex Receptacle 15A



Features

- Tamper-Resistant (TR) duplex
- Easily mounts to a one gang box
- Back and side wiring

General

Color	<ul style="list-style-type: none">• Light Almond• Amande Clair
EU RoHS Indicator	Contact Manufacturer
Series	Special Use
Style	Clock Hanger / Recessed Receptacles
Type	Duplex Receptacle
UPC	883778305702

Electrical Ratings

Current / Amperage Rating	15 A
Voltage Rating	125 V
Voltage Rating Description	125 V

Logistics

Carton Quantity 10

Product Assets

[Catalog Page - Bryant A-24 Catalog page](#)
[Catalog Page - Bryant R-2 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Literature - Concealled Connections](#)
[Literature - Home Entertainment](#)
[Literature - Residential Catalog](#)

Related Products

[RR1510I - RECESS TR DUP RCPT, 15A 125V, IVORY](#)
[RR1514W - RECES TR DUP RCPT 2G W/SNAPFIT,15A 125WH](#)
[RR1510W - RECESS TR DUP RCPT, 15A 125V, WHITE](#)
[RR1512I - RECESS TR DUP RCPT 2G W/FEED,15A 125V,IV](#)
[RR1512LA - RECESS TR DUP RCPT 2G W/FEED,15A 125V,LA](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-RR1510LA-SPEC-EN | REV 7/2023