



# TradeSelect, Straight Blade, Single Receptacle, Clock Hanger, Tamper Resistant, 15A 125V, 2-Pole 3-WireGrounding, 5-15R, Brass Plate

By Bryant  
Catalog # [RR151CHBSTR](#)

TradeSelect, Straight Blade, Single Receptacle, Clock Hanger, Tamper Resistant, 15A 125V, 2-Pole 3- WireGrounding, 5-15R, Brass Plate



## Application

Special Use Products

## General

Color	Brass
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Series	Special Use
Style	Clock Hanger / Recessed Receptacles
Type	Single Receptacle
UPC	883778302152

## Dimensions

Display Size Standard Sized Product

## Electrical Ratings

Amperage Rating	15 A
Connectivity	Back and Side Wired Screw Terminals
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	1875

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

## Certifications and Compliance

Industry Standard(s)	UL Listed
Nema Rating	5-15R

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - Bryant A-24 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)

## Related Products

[RR1510LA - RECESS TR DUP RCPT, 15A 125V, LG ALMOND](#)  
[RR201CHWTR - TradeSelect, Straight Blade, Single Receptacle, Clock Hanger, Tamper Resistant, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, White Plate](#)  
[RR1510I - RECESS TR DUP RCPT, 15A 125V, IVORY](#)  
[RR151CHITR - TradeSelect, Straight Blade Devices, Tamper Resistant Receptacle, Clock Hanger, Residential Grade, 15A 125V, 2-Pole 3-WireGrounding, 5-15R, Ivory](#)  
[RR201CHSSTR - TradeSelect, Straight Blade, Single Receptacle, Clock Hanger, Tamper Resistant, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Nickel Plate](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-RR151CHBSTR-SPEC-EN | REV 7/2023