



CLOCK HANG RECESS RCPT, 15A 125V, IV

By Bryant
Catalog # RR151CHI



CLOCK HANG RECESS RCPT, 15A 125V, IV

Features

- 15A 125V
- IV

Application

Special Use Products

General

| | |
|------------------------------|-------------------------------------------------|
| Catalog Number | RR151CHI |
| Color | Ivory |
| EU RoHS Indicator | Contact Manufacturer |
| Environmental Conditions | Indoor Dry Unless Protected By Additional Means |
| Material | Thermoplastic |
| Material - Mounting Hardware | Screw Mounting |
| Number Of Poles | 2-Pole |
| UPC | 883778100413 |

Dimensions

| | |
|--------------|------------------------|
| Display Size | Standard Sized Product |
|--------------|------------------------|

Electrical Ratings

| | |
|---------------------------|-------------------------------------|
| Amperage Rating | 15 A |
| Connectivity | Back and Side Wired Screw Terminals |
| Current / Amperage Rating | 15 A |
| Current Rating | 15 A |
| Phase | Single Phase |
| Voltage Rating | 125 VAC |
| Wattage | 1875 |

Conductor Related

| | |
|-----------------|--------------------|
| Number Of Wires | 3-Wire Grounding |
| Wire Size | #14 AWG to #12 AWG |

Certifications And Compliance

| | |
|-------------|-------|
| Nema Rating | 5-15R |
|-------------|-------|

Logistics

| | |
|-----------------|----|
| Carton Quantity | 10 |
|-----------------|----|

Product Assets

[Specifications - RR151CHI](#)