



CLOCK HANG RECESS RCPT, 15A 125V, WH

By Bryant
Catalog # [RR151CHW](#)

CLOCK HANG RECESS RCPT, 15A 125V, WH



Application

Special Use Products

General

Color	White
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
UPC	883778100420

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Amperage Rating	15 A
Connectivity	Back and Side Wired Screw Terminals
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase
Voltage Rating	125 VAC
Wattage	1875

Conductor Related

Number Of Wires	3-Wire Grounding
Wire Size	#14 AWG to #12 AWG

Certifications and Compliance

Nema Rating	5-15R
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

Related Products

[RR151CHSSTR](#) - TradeSelect, Straight Blade Devices, Receptacles, Residential Grade, Tamper Resistant Clock Hanger, 15A 125V, 5-15R, Stainless Steel

[RR201CHWTR](#) - TradeSelect, Straight Blade, Single Receptacle, Clock Hanger, Tamper Resistant, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, White Plate

[RR151CHBSTR](#) - TradeSelect, Straight Blade, Single Receptacle, Clock Hanger, Tamper Resistant, 15A 125V, 2-Pole 3-WireGrounding, 5-15R, Brass Plate

[RR1510W](#) - RECESS TR DUP RCPT, 15A 125V, WHITE

[RR151CHITR](#) - TradeSelect, Straight Blade Devices, Tamper Resistant Receptacle, Clock Hanger, Residential Grade, 15A 125V, 2-Pole 3-WireGrounding, 5-15R, Ivory



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-RR151CHW-SPEC-EN | REV 7/2023