



TradeSelect, Straight Blade, Single Receptacle, Weather and Tamper Resistant, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Light Almond

By Bryant
Catalog # RR151LAWRTR



TradeSelect, Straight Blade, Single Receptacle, Weather and Tamper Resistant, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Light Almond

Features

-
-
-

Application

Residential Receptacles

Performance

- Environmental - Operating temperature - -20°C to 60°C
- Mechanical - Terminal - Terminal screws accepts up to #12 AWG, Push wire designed for #14 AWG solid copper wire only

General

| | |
|------------------------------|---|
| Catalog Number | RR151LAWRTR |
| Color | Light Almond |
| EU RoHS Indicator | No |
| Environmental Conditions | Weather Resistant |
| Item Type | Single |
| Material | Thermoplastic |
| Material - Mounting Hardware | Screw Mounting |
| Number Of Poles | 2-Pole |
| Specifications | <ul style="list-style-type: none"> • Material - Thermoplastic • Number of Poles - 2 Pole • Product Type - Receptacle • Receptacle Type - Single |
| UPC | 883778302886 |

Dimensions

Display Size Standard Sized Product

Electrical Ratings

| | |
|----------------------------|--------------|
| Amperage Rating | 15 A |
| Connectivity | Side Wired |
| Current / Amperage Rating | 15 A |
| Current Rating | 15 A |
| Phase | Single Phase |
| Voltage Rating | 125 VAC |
| Voltage Rating Description | 125 VAC |
| Wattage | 1875 |

Conductor Related

| | |
|-----------------|--------------------|
| Number Of Wires | 3-Wire Grounding |
| Wire Size | #14 AWG to #12 AWG |

Certifications And Compliance

| | |
|-------------|-------|
| Nema Rating | 5-15R |
|-------------|-------|

Logistics

| | |
|-----------------|----|
| Carton Quantity | 10 |
|-----------------|----|

Product Assets

- [Catalog Page - WDK Z-17 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Literature - Residential Catalog](#)
- [Specifications - RR151LAWRTR](#)