



# TradeSelect, Straight Blade Devices, Receptacles, Residential Grade, Weather and Tamper Resistant Single, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R

By Bryant  
Catalog # RR151WWRTR



TradeSelect, Straight Blade Devices, Receptacles, Residential Grade, Weather and Tamper Resistant Single, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, White

## Features

- Smooth indented face appearance
- Multiple-drive Slot/Phillips/Robertson head screws
- Tough thermoplastic ultrasonically welded cover and base

## Application

Residential Receptacles

## Performance

- Environmental - Operating temperature - -20°C to 60°C
- Mechanical - Terminal - Terminal screws accepts up to #12 AWG, Push wire designed for #14 AWG solid copper wire only

## General

Catalog Number	RR151WWRTR
Color	White
EU RoHS Indicator	No
Environmental Conditions	Weather Resistant
Item Type	Single
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Specifications	<ul style="list-style-type: none"> <li>• Material - Thermoplastic</li> <li>• Number of Poles - 2 Pole</li> <li>• Product Type - Receptacle</li> <li>• Receptacle Type - Single</li> </ul>
UPC	883778302909

## Dimensions

Display Size Standard Sized Product

## Electrical Ratings

Amperage Rating	15 A
Connectivity	Side Wired
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125 VAC
Wattage	1875

## Conductor Related

Number Of Wires	3-Wire Grounding
Wire Size	#14 AWG to #12 AWG

## Certifications And Compliance

Nema Rating	5-15R
-------------	-------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

- [Catalog Page - WDK Z-17 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Literature - Residential Catalog](#)