



# TradeSelect, Straight Blade, Single Receptacle, Weather Resistant, 15A 250V, 2-Pole 3-Wire Grounding, 6-15R, White

By Bryant  
Catalog # [RR155WWR](#)



TradeSelect, Straight Blade, Single Receptacle, Weather Resistant, 15A 250V, 2-Pole 3-Wire Grounding, 6-15R, White

### Application

- Residential Receptacles

### Performance

- Environmental - Operating temperature - -20°C to 60°C
- Mechanical - Terminal - Terminal screws accepts up to #12 AWG, Push wire designed for #14 AWG solid copper wire only

### General

Catalog Number	RR155WWR
Color	White
EU RoHS Indicator	No
Environmental Conditions	Weather Resistant
Item Type	Single
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Specifications	<ul style="list-style-type: none"><li>Material - Thermoplastic</li><li>Number of Poles - 2 Pole</li><li>Product Type - Receptacle</li><li>Receptacle Type - Single</li></ul>
UPC	883778302756

### Dimensions

Display Size	Standard Sized Product
--------------	------------------------

### Electrical Ratings

Amperage Rating	15 A
Connectivity	Side Wired
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase
Voltage Rating	250V kV
Voltage Rating Description	250V kV
Wattage	3750

### Conductor Related

Number Of Wires	3-Wire Grounding
Wire Size	#14 AWG to #12 AWG

### Certifications And Compliance

Nema Rating	6-15R
-------------	-------

### Logistics

Carton Quantity	10
-----------------	----

### Product Assets

[Catalog Page - WDK Z-17 Catalog Page](#)  
[Catalogs - WDK Catalog Full 2024](#)  
[Catalogs - Bryant Full Line Catalog](#)  
[Specifications - RR155WWR](#)