



TradeSelect, Straight Blade, Duplex Receptacle, Tamper Resistant, Quick Wire Push Terminals, 15A 125V, 2- Pole 3-Wire Grounding, 5-15R, Ivory

By Bryant
Catalog # [RR15EQITR](#)



TradeSelect, Straight Blade, Duplex Receptacle, Tamper Resistant, Quick Wire Push Terminals, 15A 125V, 2- Pole 3-Wire Grounding, 5-15R, Ivory

Features

-
-
-

Application

Residential Receptacles

Performance

- Environmental - Operating temperature - -20°C to 60°C
- Mechanical - Terminal - Terminal screws accepts up to #12 AWG, Push wire designed for #14 AWG solid copper wire only

General

Catalog Number	RR15EQITR
Color	Ivory
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Traditional Duplex
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Specifications	<ul style="list-style-type: none"> • Base and Cover - Tough thermoplastic • Product Type - Receptacle • Receptacle Type - Duplex Quick Thread • Spring Material - Stainless Steel
UPC	883778301384

Dimensions

Display Size Standard Sized Product

Electrical Ratings

Amperage Rating	15 A
Connectivity	Eight Push Wire Holes
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125 VAC
Wattage	1875

Conductor Related

Number Of Wires	3-Wire Grounding
Wire Size	#14 AWG to #12 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • CSA Certified • UL Listed E2186
Nema Rating	5-15R

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - BRY A-18 Catalog Page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Specifications - RR15EQITR](#)

