



# TradeSelect, Straight Blade, Duplex Receptacle, Tamper Resistant, Quick Wire Push Terminals, 15A 125V, 2- Pole 3-Wire Grounding, 5-15R, Brown

By Bryant  
Catalog # RR15EQTR



TradeSelect, Straight Blade, Duplex Receptacle, Tamper Resistant, Quick Wire Push Terminals, 15A 125V, 2- Pole 3-Wire Grounding, 5-15R, Brown

## Features

- Smooth indented face appearance
- Tough thermoplastic ultrasonically welded cover and base
- Elongated strap with continuous plaster ears to secure device

## Application

Residential Receptacles

## Performance

- Environmental - Operating temperature - -20°C to 60°C
- Mechanical - Terminal - Terminal screws accepts up to #12 AWG, Push wire designed for #14 AWG solid copper wire only

## General

Catalog Number	RR15EQTR
Color	Brown
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Traditional Duplex
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Specifications	<ul style="list-style-type: none"> <li>• Base and Cover - Tough thermoplastic</li> <li>• Product Type - Receptacle</li> <li>• Receptacle Type - Duplex Quick Thread</li> <li>• Spring Material - Stainless Steel</li> </ul>
UPC	883778301346

## Dimensions

Display Size Standard Sized Product

## Electrical Ratings

Amperage Rating	15 A
Connectivity	Eight Push Wire Holes
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125 VAC
Wattage	1875

## Conductor Related

Number Of Wires	3-Wire Grounding
Wire Size	#14 AWG to #12 AWG

## Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"> <li>• CSA Certified</li> <li>• UL Listed E2186</li> </ul>
Nema Rating	5-15R

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - BRY A-18 Catalog Page](#)  
[Catalogs - Bryant Full Line Catalog](#)  
[Specifications - RR15EQTR](#)

