



TradeSelect, Straight Blade, Duplex Receptacle, Tamper Resistant, Cut Ears, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Light Almond

By Bryant
Catalog # RR15KLATR



TradeSelect, Straight Blade, Duplex Receptacle, Tamper Resistant, Cut Ears, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Light Almond

Application

Residential Receptacles

Performance

- Environmental - Operating temperature - -20°C to 60°C
- Mechanical - Terminal - Terminal screws accepts up to #12 AWG, Push wire designed for #14 AWG solid copper wire only

General

Catalog Number	RR15KLATR
Color	Light Almond
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Traditional Duplex
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Specifications	<ul style="list-style-type: none">• Material - Thermoplastic• Number of Poles - 2 Pole• Product Type - Receptacle• Receptacle Type - Duplex
UPC	883778301742

Dimensions

Display Size Standard Sized Product

Electrical Ratings

Amperage Rating	15 A
Connectivity	Eight Push Wire Holes
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125 VAC
Wattage	1875

Conductor Related

Number Of Wires	3-Wire Grounding
Wire Size	#14 AWG to #12 AWG

Certifications And Compliance

Nema Rating	5-15R
-------------	-------

Logistics

Carton Quantity	100
-----------------	-----

Product Assets

[Catalog Page - BRY A-18 Catalog Page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Literature - General Literature - Tamper-Resistant and Weather Resistant Receptacles](#)
[Specifications - RR15KLATR](#)