



TradeSelect, Straight Blade Devices, Receptacles, Residential Grade, Tamper Resistant Duplex, Quick Thread, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R

By Bryant
Catalog # [RR15QLATR](#)



tradeSELECT® Straight Blade Receptacle, Residential Grade, Tamper Resistant Duplex, Quick Thread, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R

Features

- Smooth indented face appearance
- Tough thermoplastic ultrasonically welded cover and base
- Elongated strap with continuous plaster ears to secure device

Application

Residential Receptacles

General

Color	<ul style="list-style-type: none"> • Light Almond • Amande pâle
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Traditional Duplex
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Performance	<ul style="list-style-type: none"> • Environmental - Operating temperature - -20°C to 60°C • Mechanical - Terminal - Terminal screws accepts up to #12 AWG, Push wire designed for #14 AWG solid copper wire only
UPC	883778301605

Dimensions

Display Size Standard Sized Product

Electrical Ratings

Amperage Rating	15 A
Connectivity	Push and Side Wire
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125 VAC
Wattage	1875

Conductor Related

Number Of Wires	3-Wire Grounding
Wire Size	#14 AWG to #12 AWG

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • CSA Certified • UL Listed E2186
----------------------	--

Nema Rating	5-15R
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant A-18 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Literature - General Literature - Tamper-Resistant and Weather Resistant Receptacles](#)



A proud member of the Hubbell Family.