



# RCPT DUP, 15A 125V, B/S WIRE QCK-PLT, WH

By Bryant  
Catalog # RR15QW

RCPT DUP, 15A 125V, B/S WIRE QCK-PLT, WH



## Features

- Smooth indented face appearance
- Multiple-drive Slot/Phillips/Robertson head screws
- Tough thermoplastic ultrasonically welded cover and base

## General

Application	Residential Receptacles
Color	White
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Traditional Duplex
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
UPC	883778110726

## Dimensions

Display Size	Standard Sized Product
--------------	------------------------

## Electrical Ratings

Amperage Rating	15 A
Connectivity	Push and Side Wire
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase
Voltage Rating	125 VAC
Wattage	1875

## Conductor Related

Number Of Wires	3-Wire Grounding
Wire Size	#14 AWG to #12 AWG

## Certifications And Compliance

Nema Rating	5-15R
-------------	-------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - WDK Z-16 Catalog Page](#)  
[Catalogs - WDK Catalog Full 2024](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRY-RR15QW-SPEC-EN | REV 6/2024