



# TradeSelect, Straight Blade Residential Grade Receptacles, Tamper Resistant Single, 20A 125V, 2- Pole 3-Wire Grounding, 5-20R, Self Grounding, Almond

By Bryant  
Catalog # [RR201ALTR](#)



TradeSelect, Straight Blade Devices, Residential Grade, Receptacles, Tamper Resistant Single, 20A 125V, 2- Pole 3-Wire Grounding, 5-20R, Self Grounding, Almond

## Features

- Smooth indented face appearance
- Multiple-drive Slot/Phillips/Robertson head screws
- Tough thermoplastic ultrasonically welded cover and base

## Application

Residential Receptacles

## General

Catalog Number	RR201ALTR
Color	Almond
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Single
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
UPC	883778301940

## Dimensions

Display Size	Standard Sized Product
--------------	------------------------

## Electrical Ratings

Amperage Rating	20 A
Connectivity	Side Wired
Current / Amperage Rating	20 A
Current Rating	20 A
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125 VAC
Wattage	2500

## Conductor Related

Number Of Wires	3-Wire Grounding
Wire Size	#12 AWG to #10 AWG

## Certifications And Compliance

Nema Rating	5-20R
-------------	-------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Literature - General Literature - Tamper-Resistant and Weather Resistant Receptacles Specifications - RR201ALTR](#)