



# TradeSelect, Straight Blade, SingleReceptacle, Clock Hanger, Tamper Resistant, 20A 125V, 2-Pole 3- WireGrounding, 5-20R, Ivory Plate

By Bryant  
Catalog # RR201CHITR



TradeSelect, Straight Blade, SingleReceptacle, Clock Hanger, Tamper Resistant, 20A 125V, 2-Pole 3- WireGrounding, 5-20R, Ivory Plate

## Features

- Clock Hanger
- Tamper Resistant

## Application

Special Use Products

## General

Catalog Number	RR201CHITR
Color	Ivory
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Series	Special Use
Style	Clock Hanger / Recessed Receptacles
Type	Single Receptacle
UPC	883778302206

## Dimensions

Display Size	Standard Sized Product
--------------	------------------------

## Electrical Ratings

Amperage Rating	20 A
Connectivity	Back and Side Wired Screw Terminals
Current / Amperage Rating	15 A
Current Rating	20 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	2500

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#12 AWG to #10 AWG

## Certifications And Compliance

Industry Standard(s)	UL Listed
Nema Rating	5-15R

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

- [Catalog Page - WDK Z-18 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Specifications - RR201CHITR](#)