



# TradeSelect, Straight Blade Devices, Residential Grade, Tamper Resistant Receptacles, Single, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R

By Bryant  
Catalog # RR201GY



TradeSelect, Straight Blade Devices, Residential Grade, Tamper Resistant Receptacles, Single, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Self Grounding, Gray

## Features

- Smooth indented face appearance
- Multiple-drive Slot/Phillips/Robertson head screws
- Tough thermoplastic ultrasonically welded cover and base

## Application

Residential Receptacles

## Performance

- Environmental - Operating temperature - -20°C to 60°C
- Mechanical - Terminal - Terminal screws accepts up to #12 AWG, Push wire designed for #14 AWG solid copper wire only

## General

Catalog Number	RR201GY
Color	Gray
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Single
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Specifications	<ul style="list-style-type: none"><li>• Material - Thermoplastic</li><li>• Number of Poles - 2 Pole</li><li>• Product Type - Receptacle</li><li>• Receptacle Type - Single</li></ul>
UPC	883778110634

## Dimensions

Display Size

Standard Sized Product

## Electrical Ratings

Amperage Rating	20 A
Connectivity	Side Wired
Current / Amperage Rating	20 A
Current Rating	20 A
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125 VAC
Wattage	2500

## Conductor Related

Number Of Wires	3-Wire Grounding
Wire Size	#12 AWG to #10 AWG

## Certifications And Compliance

Nema Rating	5-20R
-------------	-------

## Logistics

Carton Quantity	10
Pallet Quantity	9000

## Product Assets

[Catalog Page - WDK Z-17 Catalog Page](#)  
[Catalogs - WDK Catalog Full 2024](#)  
[Catalogs - Bryant Full Line Catalog](#)  
[Specifications - RR201GY](#)