



TradeSelect, Straight Blade Devices, Residential Grade, Receptacles, Single, 20A 250V, 2-Pole 3-Wire Grounding, 6-20R, Self Grounding, Brown

By Bryant
Catalog # RR205



tradeSELECT® Straight Blade Residential Grade, Single, 20A 250V, 2-Pole 3-Wire Grounding, 6-20R, Self Grounding

Application

- Residential Receptacles

Performance

- Environmental - Operating temperature - -20°C to 60°C
- Mechanical - Terminal - Terminal screws accepts up to #12 AWG, Push wire designed for #14 AWG solid copper wire only

General

Catalog Number	RR205
Color	Brown
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Single
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Specifications	<ul style="list-style-type: none"> Material - Thermoplastic Number of Poles - 2 Pole Product Type - Receptacle Receptacle Type - Single
UPC	883778300592

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Amperage Rating	20 A
Connectivity	Side Wired
Current / Amperage Rating	20 A
Current Rating	20 A
Phase	Single Phase
Voltage Rating	250V kV
Voltage Rating Description	250V kV
Wattage	5000

Conductor Related

Number Of Wires	3-Wire Grounding
Wire Size	#12 AWG to #10 AWG

Certifications And Compliance

Nema Rating	6-20R
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
Pallet Quantity	9000

Product Assets

- [Catalog Page - WDK Z-17 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Specifications - RR205](#)