



# TradeSelect, Straight Blade Devices, Residential Grade, Receptacles, Single, 20A 250V, 2-Pole 3-Wire Grounding, 6-20R, Self Grounding, White

By Bryant  
Catalog # RR205W



tradeSELECT® Straight Blade Residential Grade, Single, 20A 250V, 2-Pole 3-Wire Grounding, 6-20R, Self Grounding

## Application

- Residential Receptacles

## Performance

- Environmental - Operating temperature - -20°C to 60°C
- Mechanical - Terminal - Terminal screws accepts up to #12 AWG, Push wire designed for #14 AWG solid copper wire only

## General

Catalog Number	RR205W
Color	White
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Single
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Specifications	<ul style="list-style-type: none"><li>Material - Thermoplastic</li><li>Number of Poles - 2 Pole</li><li>Product Type - Receptacle</li><li>Receptacle Type - Single</li></ul>
UPC	883778300615

## Dimensions

Display Size	Standard Sized Product
--------------	------------------------

## Electrical Ratings

Amperage Rating	20 A
Connectivity	Side Wired
Current / Amperage Rating	20 A
Current Rating	20 A
Phase	Single Phase
Voltage Rating	250V kV
Voltage Rating Description	250V kV
Wattage	5000

## Conductor Related

Number Of Wires	3-Wire Grounding
Wire Size	#12 AWG to #10 AWG

## Certifications And Compliance

Nema Rating	6-20R
-------------	-------

## Logistics

Carton Quantity	10
Pallet Quantity	9000

## Product Assets

[Catalog Page - WDK Z-17 Catalog Page](#)  
[Catalogs - WDK Catalog Full 2024](#)  
[Catalogs - Bryant Full Line Catalog](#)  
[Specifications - RR205W](#)