



# TradeSelect, Straight Blade Devices, Residential Grade, Weather Resistant Receptacles, Single, 20A 250V, 2- Pole 3-Wire Grounding, 6-20R

By Bryant  
Catalog # [RR205WWR](#)



TradeSelect, Straight Blade Devices, Residential Grade, Weather Resistant Receptacles, Single, 20A 250V, 2- Pole 3-Wire Grounding, 6-20R, Self Grounding, White

## Features

- Smooth indented face appearance
- Multiple-drive Slot/Phillips/Robertson head screws
- Tough thermoplastic ultrasonically welded cover and base

## Application

Residential Receptacles

## General

Color	<ul style="list-style-type: none"><li>• White</li><li>• Blanc</li></ul>
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Single
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Performance	<ul style="list-style-type: none"><li>• Environmental - Operating temperature - -20°C to 60°C</li><li>• Mechanical - Terminal - Terminal screws accepts up to #12 AWG, Push wire designed for #14 AWG solid copper wire only</li></ul>
UPC	883778302824

## Dimensions

Display Size Standard Sized Product

## Electrical Ratings

Amperage Rating	20 A
Connectivity	Side Wired
Current / Amperage Rating	20 A
Current Rating	20 A
Phase	Single Phase
Voltage Rating	250V kV
Voltage Rating Description	250V kV
Wattage	5000

## Conductor Related

Number Of Wires	3-Wire Grounding
Wire Size	#12 AWG to #10 AWG

## Certifications and Compliance

Nema Rating	6-20R
-------------	-------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - Bryant A-19 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-RR205WWR-SPEC-EN | REV 7/2023