



TradeSelect, Straight Blade Devices, Residential Grade, Male Plug, 30A 125/250V, 3-Pole 3-Wire Non-Grounding, 10-30P, Polarized

By Bryant
Catalog # [RR335P](#)

tradeSELECT® Straight Blade Residential Grade Male Plug, 30A 125/250V, 3-Pole 3-Wire Non-Grounding, Polarized



General

Color	<ul style="list-style-type: none">• Black• Noir
Number Of Poles	3-Pole
Series	Commercial
Style	Heavy Duty
Type	Plugs
UPC	883778100864

Electrical Ratings

Current / Amperage Rating	50 A
Voltage Rating	125/250 V
Voltage Rating Description	125/250 V

Conductor Related

Number Of Wires	3-Wire
-----------------	--------

Certifications and Compliance

Industry Standard(s)	UL Listed
Nema Rating	10-50P

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant A-26 Catalog page](#)
[Catalog Page - Bryant A-27 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)

Related Products

[RR330 - TradeSelect, Straight Blade Devices, Residential Grade, Receptacles, Single, 30A 125/250V, 3-Pole 3-Wire Non-Grounding, 10-30R, Surface Mount, Black](#)
[RR350 - TradeSelect, Straight Blade Devices, Residential Grade, Receptacles, Single, 50A 125/250V, 3-Pole 3-Wire Non-Grounding, 10-50R, Surface Mount, Black](#)
[RR330F - TradeSelect, Straight Blade Devices, Residential Grade, Receptacles, Single, 30A 125/250V, 3-Pole 3-Wire Non-Grounding, 10-30R, Flush Mount, Black](#)
[RR350F - TradeSelect, Straight Blade Devices, Residential Grade, Receptacles, Single, 50A 125/250V, 3-Pole 3-Wire Non-Grounding, 10-50R, Flush Mount, Black](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-RR335P-SPEC-EN | REV 7/2023