



TradeSelect, Straight Blade, Single Panel Mount Receptacle, 30A 125/250V, 3-Pole 4-Wire Grounding, 14-30R, Black, With Plate

By Bryant
Catalog # [RR430WIPCN](#)



TradeSelect, Straight Blade, Single Panel Mount Receptacle, 30A 125/250V, 3-Pole 4-Wire Grounding, 14-30R, Black, With Plate

Application

Residential Grade

General

Color	<ul style="list-style-type: none">• White• Noir
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Flanged Single
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
UPC	883778301858

Dimensions

Display Size Standard Sized Product

Electrical Ratings

Amperage Rating	30 A
Connectivity	Screw Terminals
Current / Amperage Rating	30 A
Current Rating	30 A
Phase	Single Phase
Voltage Rating	125/250 VAC
Wattage	7500

Conductor Related

Number Of Wires	4-Wire Grounding
Wire Size	#10 AWG

Certifications and Compliance

Nema Rating	14-30R
-------------	--------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

Related Products

[RR430](#) - TradeSelect, Straight Blade Devices, Residential Grade, Receptacles, Single, 30A 125/250V, 3-Pole 4-Wire Grounding, 14-30R, Surface Mount, Black

[RR450](#) - TradeSelect, Straight Blade Devices, Residential Grade, Receptacles, Single, 50A 125/250V, 3-Pole 4-Wire Grounding, 14-50R, Surface Mount, Black

[RR450WIPCN](#) - TradeSelect, Straight Blade, Single Panel Mount Receptacle, 50A 125/250V, 3-Pole 4-Wire Grounding, 14-50R, Black, With Plate

[RR430FW](#) - TradeSelect, Straight Blade Devices, Residential Grade, Receptacles, Single, 30A 125/250V, 3-Pole 4-Wire Grounding, 14-30R, Flush Mount, White

[RR450FW](#) - TradeSelect, Straight Blade Devices, Residential Grade, Receptacles, Single, 50A 125/250V, 3-Pole 4-Wire Grounding, 14-50R, Flush Mount, White



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-RR430WIPCN-SPEC-EN | REV 7/2023