



# TradeSelect, Straight Blade Devices, Residential Grade, Receptacles, Single, 50A 125/250V, 3-Pole 4-Wire Grounding, 14-50R, Flush Mount, White

By Bryant  
Catalog # [RR450FW](#)



tradeSELECT® Straight Blade Residential Grade, Single, 50A 125/250V, 3-Pole 4-Wire Grounding, 14-50R, Flush Mount

## Features

- Sequenced contacts assure protection
- Catalog number, ratings and certifications molded in face
- One piece design power and ground contacts

## Application

Residential Range and Dryer Devices

## General

Color	<ul style="list-style-type: none"> <li>• Black</li> <li>• Noir</li> </ul>
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
Series	Heavy Duty
Style	Smooth Face
Type	Single Receptacle
UPC	883778100765

## Dimensions

Display Size	Standard Sized Product
--------------	------------------------

## Electrical Ratings

Amperage Rating	50 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	50 A
Current Rating	50 A
Phase	Single Phase
Voltage Rating	125/250 V
Voltage Rating Description	125/250 V
Wattage	12500

## Conductor Related

Number Of Wires	4-Wire
Wire Size	#6 AWG

## Certifications and Compliance

Industry Standard(s)	UL Listed
Nema Rating	14-50R

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - Bryant A-27 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)  
[Literature - Residential Catalog](#)

## Related Products

[SS703L - Wallplates and Boxes, Metallic Plates, 2- Gang, 1\) 2.15" Opening, 4 Bolt Mount, 430 Stainless Steel](#)  
[RR435P - TradeSelect, Straight Blade Devices, Residential Grade, Male Plug, 30A 125/250V, 3-Pole 3-Wire Non-Grounding, 14-30P, Polarized](#)  
[RR450F - TradeSelect, Straight Blade Devices, Residential Grade, Receptacles, Single, 50A 125/250V, 3-Pole 4-Wire Grounding, 14-50R, Flush Mount, Black](#)  
[RR450 - TradeSelect, Straight Blade Devices, Residential Grade, Receptacles, Single, 50A 125/250V, 3-Pole 4-Wire Grounding, 14-50R, Surface Mount, Black](#)  
[RR430 - TradeSelect, Straight Blade Devices, Residential Grade, Receptacles, Single, 30A 125/250V, 3-Pole 4-Wire Grounding, 14-30R, Surface Mount, Black](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-RR450FW-SPEC-EN | REV 7/2023