



TradeSelect, Straight Blade, Single Panel Mount Receptacle, 50A 125/250V, 3-Pole 4-Wire Grounding, 14-50R, Black

By Bryant
Catalog # [RR450PM](#)



TradeSelect, Straight Blade, Single Panel Mount Receptacle, 50A 125/250V, 3-Pole 4-Wire Grounding, 14-50R, Black

Application

Residential Range and Dryer Devices

General

Color	<ul style="list-style-type: none">BlackNoir
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
Series	Heavy Duty
Type	Single Receptacle
UPC	883778100758

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Amperage Rating	50 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	50 A
Current Rating	50 A
Phase	Single Phase
Voltage Rating	125/250 V
Voltage Rating Description	125/250 V
Wattage	12500

Conductor Related

Number Of Wires	4-Wire
Wire Size	#6 AWG

Certifications and Compliance

Industry Standard(s)	UL Listed
Nema Rating	14-50R

Logistics

Carton Quantity	50
-----------------	----

Product Assets

[Catalog Page - Bryant A-27 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)

Related Products

[RR435P - TradeSelect, Straight Blade Devices, Residential Grade, Male Plug, 30A 125/250V, 3-Pole 3-Wire Non-Grounding, 14-30P, Polarized](#)
[P724BK - Wallplate, 1-Gang, 2.15" Opening, Black](#)
[RR450WIPCN - TradeSelect, Straight Blade, Single Panel Mount Receptacle, 50A 125/250V, 3-Pole 4-Wire Grounding, 14-50R, Black, With Plate](#)
[P703BK - Wallplate, 2-Gang, 2.15" Opening, Black](#)
[RR450 - TradeSelect, Straight Blade Devices, Residential Grade, Receptacles, Single, 50A 125/250V, 3-Pole 4-Wire Grounding, 14-50R, Surface Mount, Black](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-RR450PM-SPEC-EN | REV 7/2023