



TradeSelect, Straight Blade, Single Decorator Receptacle, Self Grounding, 15A 250V, 2-Pole 3-Wire Grounding, 6-15R, Light Almond

By Bryant
Catalog # [RRD155LA](#)



TradeSelect, Straight Blade, Single Decorator Receptacle, Self Grounding, 15A 250V, 2-Pole 3-Wire Grounding, 6-15R, Light Almond

Application

Residential Receptacles

General

Color	<ul style="list-style-type: none"> Light Almond Amande Clair
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Decorator Single
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
UPC	883778300721

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Amperage Rating	15 A
Connectivity	Side Wired
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase
Voltage Rating	250V kV
Voltage Rating Description	250V kV
Wattage	3750

Conductor Related

Number Of Wires	3-Wire Grounding
Wire Size	#14 AWG to #12 AWG

Certifications and Compliance

Nema Rating	6-15R
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant A-19 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)

Related Products

[RRD205LA - TradeSelect, Single Decorator Receptacle, Self Grounding, 20A 250V, 2-Pole 3-Wire Grounding, 6-20R, Light Almond](#)
[RRD15ELA - RESI DUP DEC RCPT 15A 125V 8 HOLE LA](#)
[RRD201LA - TradeSelect, Single Decorator Receptacle, Self Grounding, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Light Almond](#)
[P26LA - Wallplate, 1-Gang, 1\) Decorator, Light Almond](#)
[RRD15SLA - TradeSelect, Straight Blade, Decorator Duplex Receptacle, Self Grounding, 15A 125V, 2-Pole 3-Wire Grounding, 5- 15R, Brown](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-RRD155LA-SPEC-EN | REV 7/2023