



TradeSelect, Single Decorator Receptacle, Self Grounding, 20A 250V, 2-Pole 3-Wire Grounding, 6-20R, Brown

By Bryant
Catalog # [RRD205](#)

TradeSelect, Single Decorator Receptacle, Self Grounding, 20A 250V, 2-Pole 3-Wire Grounding, 6-20R, Brown



Application

Residential Receptacles

General

Color	<ul style="list-style-type: none"> Brown Brun
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Decorator Single
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
UPC	883778300738

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Amperage Rating	20 A
Connectivity	Side Wired
Current / Amperage Rating	20 A
Current Rating	20 A
Phase	Single Phase
Voltage Rating	250V kV
Voltage Rating Description	250V kV
Wattage	5000

Conductor Related

Number Of Wires	3-Wire Grounding
Wire Size	#14 AWG to #12 AWG

Certifications and Compliance

Nema Rating	6-20R
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant A-19 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)

Related Products

[RRD205 - TradeSelect, Single Decorator Receptacle, Self Grounding, 20A 250V, 2-Pole 3-Wire Grounding, 6-20R, Brown](#)
[RRD205W - TradeSelect, Straight Blade Devices, Residential Grade, Receptacles, Decorator Single, 20A 250V, 2-Pole 3-Wire Grounding, 6-20R, White](#)
[RRD15 - TradeSelect, Straight Blade Devices, Residential Grade, Receptacles, Decorator Duplex, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Brown](#)
[RRD15E - RESI DUP DEC RCPT 15A 125V 8 HOLE BR](#)
[RRD205I - TradeSelect, Single Decorator Receptacle, Self Grounding, 20A 250V, 2-Pole 3-Wire Grounding, 6-20R, Ivory](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-RRD205-SPEC-EN | REV 7/2023