



TradeSelect, Inline Cord Switch, Light Duty, 6A 125V, White

By Bryant
Catalog # [RS100W](#)

TradeSelect, Inline Cord Switch, Light Duty, 6A 125V, White



General

Color	<ul style="list-style-type: none">WhiteBlanc
Series	Accessories
Style	Mini
Type	In-Line Cord Switches
UPC	883778112393

Electrical Ratings

Amperage Rating	6 A
Current / Amperage Rating	6 A
Voltage Rating	125 VAC
Voltage Rating Description	125 VAC

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - WDK Z-18 Catalog Page](#)
[Catalogs - Wiring Device-Kellems Full Catalog](#)
[Catalogs - Bryant Full Line Catalog](#)
[Sales Drawings - WDK_RS100W_DRAWING_PDF](#)

Related Products

[RD600RW - Switches and Lighting Controls, Dimmer, Rotary, Single Pole, 600W 120V AC, White](#)
[RS101W - TradeSelect, Inline Cord Switch, Heavy Duty, 6A 125V, White](#)
[RD600RI - Switches and Lighting Controls, Dimmer, Rotary, Single Pole, 600W 120V AC, Ivory](#)
[RS101I - TradeSelect, Inline Cord Switch, Heavy Duty, 6A 125V, Ivory](#)
[RD600PDK - Switches and Lighting Controls, Dimmer, Rotary, Single Pole, 600W 120V AC, Ivory or White](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-RS100W-SPEC-EN | REV 7/2023