



## TradeSelect, Inline Cord Switch, Heavy Duty, 6A 125V, White

By Bryant  
Catalog # [RS101W](#)



TradeSelect, Inline Cord Switch, Heavy Duty, 6A 125V, White

### General

Color	<ul style="list-style-type: none"><li>• White</li><li>• Blanc</li></ul>
Series	Accessories
Style	Heavy Duty
Type	In-Line Cord Switches
UPC	883778112379

### Electrical Ratings

Amperage Rating	6 A
Current / Amperage Rating	6 A
Voltage Rating	125 VAC
Voltage Rating Description	125 VAC

### Logistics

Carton Quantity	10
-----------------	----

### Product Assets

[Catalog Page - WDK Z-18 Catalog Page](#)  
[Catalogs - Wiring Device-Kellems Full Catalog](#)  
[Catalogs - Bryant Full Line Catalog](#)  
[Sales Drawings - WDK\\_RS101\\_DRAWING\\_PDF](#)

### Related Products

[RS101I - TradeSelect, Inline Cord Switch, Heavy Duty, 6A 125V, Ivory](#)  
[RD600RW - Switches and Lighting Controls, Dimmer, Rotary, Single Pole, 600W 120V AC, White](#)  
[RS100W - TradeSelect, Inline Cord Switch, Light Duty, 6A 125V, White](#)  
[RD600PDK - Switches and Lighting Controls, Dimmer, Rotary, Single Pole, 600W 120V AC, Ivory or White](#)  
[RD600RI - Switches and Lighting Controls, Dimmer, Rotary, Single Pole, 600W 120V AC, Ivory](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-RS101W-SPEC-EN | REV 7/2023