



TradeSelect, Decorator Switch, Residential Grade, Rocker Switch, General Purpose AC, Illuminated Single Pole, 15A 120/277V AC, Push Back and Side

By Bryant

Catalog # [RSD115ILW](#)



tradeSELECT® Decorator Switch, Residential Grade, Rocker Switch, General Purpose AC, Illuminated Single-Pole, 15A 120/277V AC, Push Back and Side

Performance

- Electrical - Dielectric voltage - Withstands 1,500V AC minimum for 1 minute
- Electrical - Endurance - 30,000 cycles minimum
- Electrical - Max. working voltage - 120V
- Electrical - Overload - 1.5 times rating
- Environmental - Flammability - UL V0
- Environmental - Operating temperatures - Maximum continuous 60°C
- minimum -20°C (without impact)
- Mechanical - Terminal accommodation - Back and side wire: #14 AWG min. - #12 AWG max. solid and stranded copper wire only
- push wire: #14 AWG solid copper wire only

General

| | |
|-------------------|------------------------------------------------------------------------------------------------------------|
| Catalog Number | RSD115ILW |
| EU RoHS Indicator | Yes |
| Specifications | <ul style="list-style-type: none"> • Base and body - PVC • Contacts - Copper alloy |

- Mounting strap - Galvanized steel
- Rocker - Polycarbonate
- Terminal screws - Steel
- Terminals - Brass

UPC

883778101182

Certifications And Compliance

| | |
|----------------------|-------------------------------------------------------------------------------------------------------|
| Industry Standard(s) | <ul style="list-style-type: none"> • CSA Certified • Listed to UL Standard 20 |
|----------------------|-------------------------------------------------------------------------------------------------------|

Logistics

| | |
|-----------------|------|
| Carton Quantity | 10 |
| Pallet Quantity | 8000 |

Product Assets

- [Catalog Page - WDK Z-3 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Literature - Residential Catalog](#)
- [Specifications - RSD115ILW](#)