



TradeSelect, Switches and Lighting Controls, Rocker, Marked "On Off", Single Pole, 15A 120/277V AC, Light Almond

By Bryant
Catalog # RSD115LAM



TradeSelect, Switches and Lighting Controls, Rocker, Marked "On Off", Single Pole, 15A 120/277V AC, Light Almond

Features

-
-
-

Performance

- Electrical - Dielectric voltage - Withstands 1,500V AC minimum for 1 minute
- Electrical - Endurance - 30,000 cycles minimum
- Electrical - Max. working voltage - 120V
- Electrical - Overload - 1.5 times rating
- Environmental - Flammability - UL V0
- Environmental - Operating temperatures - Maximum continuous 60°C
- minimum -20°C (without impact)
- Mechanical - Terminal accommodation - Back and side wire: #14 AWG min. - #12 AWG max. solid and stranded copper wire only
- push wire: #14 AWG solid copper wire only

General

Catalog Number
EU RoHS Indicator
Specifications

RSD115LAM
Yes
• Base and body - PVC
• Contacts - Copper alloy
• Mounting strap - Galvanized steel
• Rocker - Polycarbonate
• Terminal screws - Steel
• Terminals - Brass
883778303753

UPC

Certifications And Compliance

Industry Standard(s)
• CSA Certified
• Listed to UL Standard 20

Logistics

Carton Quantity 10

Product Assets

[Catalog Page - WDK Z-3 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Specifications - RSD115LAM](#)