



TradeSelect, Switches and Lighting Control, Rocker, Double Pole, 15A 120/277V AC, Light Almond

By Bryant
Catalog # [RSD215LA](#)



TradeSelect, Switches and Lighting Control, Rocker, Double Pole, 15A 120/277V AC, Light Almond

Features

- Smooth, quiet rocker
- Self-grounding feature is standard
- Ultrasonically welded cover and base

Performance

- Electrical - Dielectric voltage - Withstands 1,500V AC minimum for 1 minute
- Electrical - Endurance - 30,000 cycles minimum
- Electrical - Max. working voltage - 120V
- Electrical - Overload - 1.5 times rating
- Environmental - Flammability - UL V0
- Environmental - Operating temperatures - Maximum continuous 60°C
- minimum -20°C (without impact)
- Mechanical - Terminal accommodation - Back and side wire: #14 AWG min. - #12 AWG max. solid and stranded copper wire only
- push wire: #14 AWG solid copper wire only

General

Catalog Number RSD215LA

EU RoHS Indicator Specifications

Yes

- Base and body - PVC
- Contacts - Copper alloy
- Mounting strap - Galvanized steel
- Rocker - Polycarbonate
- Terminal screws - Steel
- Terminals - Brass

UPC

883778119446

Certifications And Compliance

Industry Standard(s)

- CSA Certified
- UL Listed E3896

Logistics

Carton Quantity

10

Product Assets

[Catalog Page - WDK Z-3 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Catalogs - Bryant Full Line Catalog](#)
[Specifications - RSD215LA](#)



A Hubbell brand