



TradeSelect, Decorator Switch, Residential Grade, Rocker Switch, General Purpose AC, Double Pole, 15A 120/277V AC, Push Back and Side Wired

By Bryant
Catalog # [RSD215W](#)

tradeSELECT® Decorator Switch, Residential Grade, Rocker Switch, General Purpose AC, Double-Pole, 15A 120/277V AC Push Back and Side Wired



Features

- Smooth, quiet rocker
- Self-grounding feature is standard
- Ultrasonically welded cover and base

General

- Performance
- Electrical - Dielectric voltage - Withstands 1,500V AC minimum for 1 minute
 - Electrical - Endurance - 30,000 cycles minimum
 - Electrical - Max. working voltage - 120V
 - Electrical - Overload - 1.5 times rating
 - Environmental - Flammability - UL V0
 - Environmental - Operating temperatures - Maximum continuous 60°C
 - minimum -20°C (without impact)
 - Mechanical - Terminal accommodation - Back and side wire: #14 AWG min. - #12 AWG max. solid and stranded copper wire only
 - push wire: #14 AWG solid copper wire only

UPC 883778101380

Certifications and Compliance

- Industry Standard(s)
- CSA Certified
 - UL Listed E3896

Logistics

Carton Quantity 10

Product Assets

[Catalog Page - Bryant E-6 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)

Related Products

- [RSD215BK - TradeSelect, Switches and Lighting Control, Rocker, Double Pole, 15A 120/277V AC, Black](#)
- [RSD215I - TradeSelect, Switches and Lighting Control, Rocker, Double Pole, 15A 120/277V AC, Ivory](#)
- [RSD315W - TradeSelect, Decorator Switch, Residential Grade, Rocker Switch, General Purpose AC, Three Way, 15A 120/277V AC, Push Back and Side Wired](#)
- [RSD115WM - TradeSelect, Switches and Lighting Controls, Rocker, Marked "On Off", Single Pole, 15A 120/277V AC, White](#)
- [RSD215AL - TradeSelect, Switches and Lighting Control, Rocker, Double Pole, 15A 120/277V AC, Almond](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-RSD215W-SPEC-EN | REV 7/2023