



TradeSelect, Decorator Switch, Residential Grade, Rocker Switch, General Purpose AC, Three Way, 15A 120/277V AC, Push Bac kand Side Wired

By Bryant
Catalog # RSD315I



tradeSELECT® Decorator Switch, Residential Grade, Rocker Switch, General Purpose AC, Three Way, 15A 120/277V AC, Push Bac kand Side Wired

Performance

- Electrical - Dielectric voltage - Withstands 1,500V AC minimum for 1 minute
- Electrical - Endurance - 30,000 cycles minimum
- Electrical - Max. working voltage - 120V
- Electrical - Overload - 1.5 times rating
- Environmental - Flammability - UL V0
- Environmental - Operating temperatures - Maximum continuous 60°C
- minimum -20°C (without impact)
- Mechanical - Terminal accommodation - Back and side wire: #14 AWG min. - #12 AWG max. solid and stranded copper wire only
- push wire: #14 AWG solid copper wire only

General

Catalog Number	RSD315I
EU RoHS Indicator	Yes
Specifications	<ul style="list-style-type: none">• Base and body - PVC• Contacts - Copper alloy

- Mounting strap - Galvanized steel
- Rocker - Polycarbonate
- Terminal screws - Steel
- Terminals - Brass

UPC

883778101243

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• CSA Certified• UL Listed E3896
----------------------	---

Logistics

Carton Quantity	10
Pallet Quantity	9000

Product Assets

- [Catalog Page - WDK Z-3 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Literature - Residential Catalog](#)
- [Specifications - RSD315I](#)