



# TradeSelect, Decorator Switch, Residential Grade, Rocker Switch, General Purpose AC, Illuminated Three Way, 15A 120/277V AC, Push and Side Wired

By Bryant  
Catalog # [RSD315ILI](#)



TradeSelect, Switches and Lighting Controls, Decorator Switch,  
Residential Grade, Rocker Switch, General Purpose AC,  
Illuminated Three Way, 15A 120/277V AC Push and Side Wired

## Performance

- Electrical - Dielectric voltage - Withstands 1,500V AC minimum for 1 minute
- Electrical - Endurance - 30,000 cycles minimum
- Electrical - Max. working voltage - 120V
- Electrical - Overload - 1.5 times rating
- Environmental - Flammability - UL V0
- Environmental - Operating temperatures - Maximum continuous 60°C  
minimum -20°C (without impact)
- Mechanical - Terminal accommodation - Back and side wire:  
#14 AWG min. - #12 AWG max. solid and stranded copper wire only
- push wire: #14 AWG solid copper wire only

## General

Catalog Number	RSD315ILI
EU RoHS Indicator	Yes
Specifications	<ul style="list-style-type: none"><li>• Base and body - PVC</li><li>• Contacts - Copper alloy</li></ul>

- Mounting strap - Galvanized steel
  - Rocker - Polycarbonate
  - Terminal screws - Steel
  - Terminals - Brass
- UPC  
883778101298

## Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• CSA Certified</li><li>• UL Listed E3896</li></ul>
----------------------	---

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

- [Catalog Page - WDK Z-3 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Literature - Residential Catalog](#)
- [Specifications - RSD315ILI](#)