



# TradeSelect, Switches and Lighting Control, Speed Control, Slider, Single Pole, 1.5A 120V AC, Light Almond

By Bryant  
Catalog # [RSFSQFLA](#)

TradeSelect, Switches and Lighting Control, Speed Control, Slider, Single Pole, 1.5A 120V AC, Light Almond



## General

Application - For Use On	Only use with Compatible Dimmable Bulbs
Color	<ul style="list-style-type: none"><li>Light Almond</li><li>Amande Clair</li></ul>
Construction	Metal Strap, Polycarbonate Front
Environmental Conditions	Indoor Use Only
Number Of Poles	Single Pole
Number of Gang(s)	1-Gang
Operating Temperature	32 Deg F to 104 Deg F (0 Deg C to 40 Deg C)
Orientation	Vertical
Style	Slider Fan Control
Type	Fan Control
UPC	883778116551

## Dimensions

Depth	1.3 in
Height	4.1 in
Width	2.2 in

## Electrical Ratings

Amperage Rating	1.5 A
Voltage Rating	120 VAC
Voltage Rating Description	120V AC
Wattage	180 W

## Certifications and Compliance

Industry Standard(s)	CSA Certified
----------------------	---------------

## Logistics

Carton Quantity	6
-----------------	---

## Product Assets

[Catalog Page - Bryant F-15 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)

## Related Products

- [RSFSQFI - TradeSelect, Switches and Lighting Control, Speed Control, Slider, Single Pole, 1.5A 120V AC, Ivory](#)
- [RAYFSQFW - Switches and Lighting Control, Residential Grade, Motor Speed Control, Toggle Type, Single Pole, 15A 120V AC, White](#)
- [RAYFSQFI - Switches and Lighting Control, Residential Grade, Motor Speed Control, Toggle Type, Single Pole, 15A 120V AC, Ivory](#)
- [RSFSQFW - TradeSelect, Switches and Lighting Control, Residential Grade, Motor Speed Control, Slider Type, Single Pole, 1.5A 120V AC, White](#)
- [RAYFSQFLA - Switches and Lighting Control, Residential Grade, Motor Speed Control, Toggle Type, Single Pole, 15A 120V AC, Light Almond](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-RSFSQFLA-SPEC-EN | REV 7/2023