



TradeSelect, Switches and Lighting Control, Dimmers, Replacement Slider Knobs, Ivory

By Bryant
Catalog # [RSKI](#)



TradeSelect, Switches and Lighting Control, Dimmers,
Replacement Slider Knobs, Ivory

General

Color	<ul style="list-style-type: none">IvoryIvoire
Construction	Polycarbonate
Environmental Conditions	Indoor Use Only
Operating Temperature	32 Deg F to 104 Deg F (0 Deg C to 40 Deg C)
Orientation	Vertical
Style	Replacement Knobs
UPC	883778116773

Certifications and Compliance

Industry Standard(s)	CSA Certified
----------------------	---------------

Logistics

Carton Quantity	6
-----------------	---

Product Assets

[Catalog Page - Bryant F-15 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)

Related Products

[RAYFSQFW - Switches and Lighting Control, Residential Grade, Motor Speed Control, Toggle Type, Single Pole, 15A 120V AC, White](#)

[RSFSQFI - TradeSelect, Switches and Lighting Control, Speed Control, Slider, Single Pole, 1.5A 120V AC, Ivory](#)

[RAYFSQFI - Switches and Lighting Control, Residential Grade, Motor Speed Control, Toggle Type, Single Pole, 15A 120V AC, Ivory](#)

[RSFSQFLA - TradeSelect, Switches and Lighting Control, Speed Control, Slider, Single Pole, 1.5A 120V AC, Light Almond](#)

[RSFSQFW - TradeSelect, Switches and Lighting Control, Residential Grade, Motor Speed Control, Slider Type, Single Pole, 1.5A 120V AC, White](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-RSKI-SPEC-EN | REV 7/2023