



TradeSelect, Switches and Lighting Control, Dimmers, Replacement Slider Knobs, Light Almond

By Bryant
Catalog # [RSKLA](#)



TradeSelect, Switches and Lighting Control, Dimmers,
Replacement Slider Knobs, Light Almond

General

| | |
|--------------------------|---|
| Color | <ul style="list-style-type: none">Light AlmondAmande Clair |
| Construction | Polycarbonate |
| Environmental Conditions | Indoor Use Only |
| Operating Temperature | 32 Deg F to 104 Deg F (0 Deg C to 40 Deg C) |
| Orientation | Vertical |
| Style | Replacement Knobs |
| UPC | 883778116797 |

Certifications and Compliance

| | |
|----------------------|---------------|
| Industry Standard(s) | CSA Certified |
|----------------------|---------------|

Logistics

| | |
|-----------------|---|
| Carton Quantity | 6 |
|-----------------|---|

Product Assets

[Catalog Page - Bryant F-15 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)

Related Products

[RSKI - TradeSelect, Switches and Lighting Control, Dimmers, Replacement Slider Knobs, Ivory](#)
[RAYFSQFI - Switches and Lighting Control, Residential Grade, Motor Speed Control, Toggle Type, Single Pole, 15A 120V AC, Ivory](#)
[RSFSQFLA - TradeSelect, Switches and Lighting Control, Speed Control, Slider, Single Pole, 1.5A 120V AC, Light Almond](#)
[RSKW - TradeSelect, Switches and Lighting Control, Dimmers, Replacement Slider Knobs, White](#)
[RSKLA - TradeSelect, Switches and Lighting Control, Dimmers, Replacement Slider Knobs, Light Almond](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-RSKLA-SPEC-EN | REV 7/2023