



## TradeSelect, Cube Tap, 15A 125V AC, 2- Pole 3-Wire Grounding, 5-15R, White

By Bryant  
Catalog # [RT100W](#)



TradeSelect, Cube Tap, 15A 125V AC, 2- Pole 3-Wire Grounding, 5-15R, White

### General

Color	White
Insulation	Insulated Body
Item Type	Adapters
Material	Composite
Operating Temperature	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Series	Taps & Adaptors
UPC	883778112461

### Electrical Ratings

Amperage Rating	15 A
Current / Amperage Rating	15 A
Current Rating	15 A
Voltage Rating	125 VAC
Wattage	1875

### Certifications and Compliance

Industry Standard(s)	C/US UL Listed
----------------------	----------------

### Logistics

Carton Quantity	10
-----------------	----

### Product Assets

[Catalog Page - Bryant A-25 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)

### Related Products

[RP123W - TradeSelect, Straight Blade Devices, Residential Grade, Male Plug, 15A 125V, 2-Pole 2-Wire Non-Grounding, 1-15P, Polarized, Zip Cord, White](#)  
[RP123PW - Plug, 15A 125V, 2W, POLAR ZIPCORD, White](#)  
[RP101BK - Straight Blade Devices, Residential Grade, Male Plug, 15A 125V, 2-Pole 2-Wire Non-Grounding, 1-15P, Polarized](#)  
[RT200 - Adapters, Residential Grade, 15A 125V 2- Pole 2-Wire Non-Grounding Male to 15A 125V 2-Pole 3-Wire Grounding Female, Gray](#)  
[RT300W - Adapters, Residential Grade, Single to 3 Outlet, 15A 125V 2-Pole 3-Wire Grounding, Ivory](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-RT100W-SPEC-EN | REV 7/2023