



Adapters, Residential Grade, Single to 3 Outlet, 15A 125V 2-Pole 3-Wire Grounding, Ivory

By Bryant
Catalog # [RT300W](#)

Adapters, Residential Grade, Single to 3 Outlet, 15A 125V 2-Pole 3-Wire Grounding, Ivory



Application

Three Outlet Plug-In

General

Color	<ul style="list-style-type: none">• White• Blanc
Insulation	Insulated Body
Item Type	Taps
Material	Composite
Operating Temperature	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Series	Taps & Adaptors
UPC	883778112430

Electrical Ratings

Amperage Rating	15 A
Current / Amperage Rating	15 A
Current Rating	15 A
Voltage Rating	125 VAC
Wattage	1875

Certifications and Compliance

Industry Standard(s)	C/US UL Listed
----------------------	----------------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant A-25 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)

Related Products

- [RT200 - Adapters, Residential Grade, 15A 125V 2- Pole 2-Wire Non-Grounding Male to 15A 125V 2-Pole 3-Wire Grounding Female, Gray](#)
- [RT100W - TradeSelect, Cube Tap, 15A 125V AC, 2- Pole 3-Wire Grounding, 5-15R, White](#)
- [RP123W - TradeSelect, Straight Blade Devices, Residential Grade, Male Plug, 15A 125V, 2-Pole 2-Wire Non-Grounding, 1-15P, Polarized, Zip Cord, White](#)
- [RP648 - TradeSelect, Straight Blade Devices, Replacement Plug, 15A 125V, 2-Pole 2-Wire Grounding, 1-15P, White](#)
- [9053AB - Locking Devices, Locking Devices, Accessories, Straight Adapter, NEMA 3-Wire Male to 5-15R Female, 2-Pole 3-Wire Grounding, White](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-RT300W-SPEC-EN | REV 7/2023