



# TradeSelect, Cube Tap, Duplex to 6 Outlet, 15A 125V AC, 2-Pole 3-Wire Grounding, 5-15R, White

By Bryant  
Catalog # [RT600W](#)

tradeSELECT® Cube Tap, Duplex to 6 Outlet, 15A 125V AC, 2-Pole 3-Wire Grounding, 5-15R



## Application

Six Outlet Plug-In

## General

Color	<ul style="list-style-type: none"> <li>• White</li> <li>• Blanc</li> </ul>
Insulation	Insulated Body
Item Type	Taps
Material	Composite
Operating Temperature	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Series	Taps & Adaptors
UPC	883778112416

## Electrical Ratings

Amperage Rating	15 A
Current / Amperage Rating	15 A
Current Rating	15 A
Voltage Rating	125 VAC
Wattage	1875

## Certifications and Compliance

Industry Standard(s) C/US UL Listed

## Logistics

Carton Quantity 10

## Product Assets

[Catalog Page - Bryant A-25 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)

## Related Products

[RP101W - TradeSelect, Straight Blade, Male Plug, Light Duty, Polarized, 15A 125V, 2-Pole 2-Wire Non-Grounding, 1-15P, White](#)  
[RP123PI - Plug, 15A 125V, 2W, POLAR ZIPCORD, Ivory](#)  
[RP123I - TradeSelect, Straight Blade Devices, Residential Grade, Male Plug, 15A 125V, 2-Pole 2-Wire Non-Grounding, 1-15P, Polarized, Zip Cord, Ivory](#)  
[RT100W - TradeSelect, Cube Tap, 15A 125V AC, 2- Pole 3-Wire Grounding, 5-15R, White](#)  
[RP102BK - TradeSelect, Straight Blade, Female Connector, Zip Cord, Polarized, 15A 125V, 2-Pole 2-Wire Non-Grounding, 1-15R, Black](#)



A proud member of the Hubbell Family.