



Wallplates and Boxes, Metallic Plates, 1- Gang, 1) 1.40" Opening, Standard Size, Aluminum

By Bryant
Catalog # SA7

Twist-Lock® Devices, Wallplates, 1-Gang, Accessories for 15 Amp 2 and 3 Wire Devices, Aluminum .05 in. (1.3), horizontal brushed finish



Features

- Used with Single Receptacles with Face Dia. 1.40" (35.6)

Application

Protection against contact of live terminals and wiring.
Provides finished look to installation.

General

Construction	Stamped
Cutout	1) 1.40" Opening
EU RoHS Indicator	Yes
Item Type	Wallplates, 1-Gang
Material	Aluminum
Material - Mounting Hardware	Screw Mounting
Number of Gang(s)	1-Gang
Operating Temperature	-40°C to 85 °C
Orientation	Vertical Mount
Size	Standard
Style	1-Single - 1.40 in. Hole
Type	<ul style="list-style-type: none">• Single• Single
UPC	883778200045

Dimensions

Display Size	Standard Sized
Thickness	0.05
Weight	0.35 lb

Certifications and Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant Q-7 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Literature - General Literature - Stainless Steel Wallplates](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-SA7-SPEC-EN | REV 7/2023