



Wallplates and Boxes, Metallic Plates, 2- Gang, 2) Toggles, Standard Size, Chrome Plated Steel

By Bryant
Catalog # SCH2



Wallplates and Boxes, Metallic Plates, 2- Gang, 2) Toggles, Standard Size, Chrome Plated Steel

Features

- Non-magnetic and corrosion resistant
- Finish is lacquer coated to inhibit oxidation
- Protective plastic film helps to prevent scratches and damage

Application

Protection against contact of live terminals and wiring. Provides finished look to installation.

General

Catalog Number	SCH2
Construction	Stamped
Cutout	2) Toggle
EU RoHS Indicator	Yes
Item Type	Screw Mount
Material	Chrome
Material - Mounting Hardware	Screw Mounting
Number of Gang(s)	2-Gang
Orientation	Vertical Mount
Size	Standard
Specifications	<ul style="list-style-type: none"> • Appearance - Polished • Mounting Screws - 302/304 SS, Slotted Head

- Plate Material - Chrome
 - Plate Openings - Toggle switch
 - Plate Type - 2-Gang 2-Toggle Toggle
- UPC 883778200557

Style
Type
UPC

Dimensions

Display Size	Standard Sized
Thickness	0.03

Certifications And Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - WDK N-6 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Literature - General Literature - Stainless Steel Wallplates Specifications - SCH2](#)