



# Wallplates and Boxes, Metallic Plates, 2- Gang, 2) Toggles, Standard Size, Chrome Plated Steel

By Bryant  
Catalog # SCH2



Wallplates and Boxes, Metallic Plates, 2- Gang, 2) Toggles, Standard Size, Chrome Plated Steel

### Features

- Non-magnetic and corrosion resistant
- Finish is lacquer coated to inhibit oxidation
- Protective plastic film helps to prevent scratches and damage

### Application

Protection against contact of live terminals and wiring. Provides finished look to installation.

### General

Catalog Number	SCH2
Construction	Stamped
Cutout	2) Toggle
EU RoHS Indicator	Yes
Item Type	Screw Mount
Material	Chrome
Material - Mounting Hardware	Screw Mounting
Number of Gang(s)	2-Gang
Orientation	Vertical Mount
Size	Standard
Specifications	<ul style="list-style-type: none"> <li>• Appearance - Polished</li> <li>• Mounting Screws - 302/304 SS, Slotted Head</li> </ul>

- Plate Material - Chrome
  - Plate Openings - Toggle switch
  - Plate Type - 2-Gang 2-Toggle Toggle
- UPC 883778200557

Style  
Type  
UPC

### Dimensions

Display Size	Standard Sized
Thickness	0.03

### Certifications And Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

### Logistics

Carton Quantity	10
-----------------	----

### Product Assets

- [Catalog Page - WDK N-6 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Literature - General Literature - Stainless Steel Wallplates Specifications - SCH2](#)