



Snap-Fit, Inline Coupler, Cat6, Slim, White

By Bryant
Catalog # [SFC6W](#)

Snap-Fit, Inline Coupler, Cat6, Slim, White



Application

Snap-Fit Category 6 Coupler

General

Color	<ul style="list-style-type: none">WhiteBlanc
Contact	Beryllium Copper
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	iSTATION RCA and Data Keystone Connectors
Material - Mounting Hardware	Snap-On- Snap-Fit
Performance	Cat 6
Series	Cat 6
Temperature Rating	Per TIA
Type	Data
UPC	662620211428

Dimensions

Display Size Standard Sized Product

Electrical Ratings

Connectivity	Plug-N-Play
Contact Resistance	100 Ohm
Withstand Voltage	1000V RMS, 1414V DC

Logistics

Carton Quantity 25

Product Assets

[Catalog Page - Bryant R-8 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-SFC6W-SPEC-EN | REV 7/2023