



RCA Connector, Female to Female, Orange Insulator, White Housing

By Bryant
Catalog # [SFRCORFFW](#)

RCA Connector, Female to Female, Orange Insulator, White Housing



Application

Snap-Fit RCA Jack

General

Contact	Beryllium Copper
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	iSTATION RCA and Data Keystone Connectors
Material - Mounting Hardware	Snap-On- Snap-Fit
Style	Orange Insulator
Temperature Rating	Per TIA
Type	RCA, Pass-Thru, F to F Coupler
UPC	662620286273

Dimensions

Display Size Standard Sized Product

Electrical Ratings

Connectivity	Plug-N-Play
Contact Resistance	100 Ohm
Withstand Voltage	1000V RMS, 1414V DC

Logistics

Carton Quantity 25

Product Assets

[Catalog Page - Bryant R-10 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-SFRCORFFW-SPEC-EN | REV 7/2023