




## Recessed RCA Connector, Orange Insulator, Office White Housing

By Bryant  
Catalog # [SFRCORROW](#)

Recessed RCA Connector, Orange Insulator, Office White Housing



### Application

Snap-Fit RCA Jack, Recessed

### General

Contact	Beryllium Copper
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	iSTATION RCA and Data Keystone Connectors
Material - Mounting Hardware	Snap-On- Snap-Fit
Style	Orange Insulator
Temperature Rating	Per TIA
Type	RCA, Pass-Thru, Recessed
UPC	662620286600

### Dimensions

Display Size Standard Sized Product

### Electrical Ratings

Connectivity	Plug-N-Play
Contact Resistance	100 Ohm
Withstand Voltage	1000V RMS, 1414V DC

### Logistics

Carton Quantity 25

### Product Assets

[Catalog Page - Bryant R-10 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-SFRCORROW-SPEC-EN | REV 7/2023