



Wire and Cable Management, Support Grips, Heavy Duty, Single Eye, Tin-Coated Bronze, 0.75-0.99"

By Bryant
Catalog # [SHC075U](#)

Wire and Cable Management, Support Grips, Heavy Duty,
Single Eye, Tin-Coated Bronze, 0.75-0.99"



Application

Single Eye

General

Approx Breaking Strength	2,820 lbs
Construction	Woven
Material	Bronze, Tin Coated
Material - Mounting Hardware	Screw Hook or Beam Clamp
OEM Brand Name	Hubbell Bryant
Series	Heavy Duty
Style	Closed Mesh, Double Weave
Type	Single Eye
UPC	781786244221

Conductor Related

Cable Diameter Range	0.75 in-0.99 in
Cable Size	.75-.99" (1.90-2.51)

Logistics

Carton Quantity 40

Product Assets

[Catalog Page - Bryant N-9 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)

Related Products

- [SHC250DES - Wire and Cable Management, Support Grips, Heavy Duty, Double Eye, Stainless Steel, 2.50-2.99"](#)
- [SHC250 - Wire and Cable Management, Support Grips, Heavy Duty, Double Eye, Tin-Coated Bronze, 2.50-2.99"](#)
- [SHC075 - Wire and Cable Management, Support Grips, Heavy Duty, Double Eye, Tin-Coated Bronze, 0.75-0.99"](#)
- [SHC300 - Wire and Cable Management, Support Grips, Heavy Duty, Double Eye, Tin-Coated Bronze, 3.00-3.49"](#)
- [SHC400 - Wire and Cable Management, Support Grips, Heavy Duty, Double Eye, Tin-Coated Bronze, 4.00-4.49"](#)



A proud member of the Hubbell Family.