



Wire and Cable Management, Support Grips, Heavy Duty, Single Eye, Tin-Coated Bronze, 1.00-1.24"

By Bryant
Catalog # [SHC100U](#)

Wire and Cable Management, Support Grips, Heavy Duty, Single Eye, Tin-Coated Bronze, 1.00-1.24"



Application

Single Eye

General

Approx Breaking Strength	4,280 lbs
Construction	Woven
Material	Bronze, Tin Coated
Material - Mounting Hardware	Screw Hook or Beam Clamp
OEM Brand Name	Hubbell Bryant
Series	Heavy Duty
Style	Closed Mesh, Double Weave
Type	Single Eye
UPC	781786244443

Conductor Related

Cable Diameter Range	1-1.24 in
Cable Size	1.00-1.24" (2.54-3.15)

Logistics

Carton Quantity 5

Product Assets

[Catalog Page - Bryant N-9 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)

Related Products

- [SHC100 - Wire and Cable Management, Support Grips, Heavy Duty, Double Eye, Tin-Coated Bronze, 1.00-1.24"](#)
- [SHC200 - Wire and Cable Management, Support Grips, Heavy Duty, Double Eye, Tin-Coated Bronze, 2.00-2.49"](#)
- [SHC075 - Wire and Cable Management, Support Grips, Heavy Duty, Double Eye, Tin-Coated Bronze, 0.75-0.99"](#)
- [SHC250DES - Wire and Cable Management, Support Grips, Heavy Duty, Double Eye, Stainless Steel, 2.50-2.99"](#)
- [SHC450 - Wire and Cable Management, Support Grips, Heavy Duty, Double Eye, Tin-Coated Bronze, 4.50-5.00"](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-SHC100U-SPEC-EN | REV 7/2023