



# Wire and Cable Management, Support Grips, Heavy Duty, Double Eye, Tin-Coated Bronze, 2.00-2.49"

By Bryant  
Catalog # [SHC200](#)

Wire and Cable Management, Support Grips, Heavy Duty,  
Double Eye, Tin-Coated Bronze, 2.00-2.49"



## Application

Double Eye

## General

Approx Breaking Strength	8,050 lbs
Construction	Woven
Material	Bronze, Tin Coated
Material - Mounting Hardware	Screw Hook or Beam Clamp
OEM Brand Name	Hubbell Bryant
Series	Heavy Duty
Style	Closed Mesh, Double Weave
Type	Double Eye
UPC	781786244047

## Conductor Related

Cable Diameter Range	2 in-2.49 in
Cable Size	2.00-2.49" (5.08-6.32)

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - Bryant N-9 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)  
[Literature - WIRING\\_WLFVM034](#)  
[Literature - Wiring\\_WLFVM032](#)  
[Literature - Wiring\\_WLBVM044](#)  
[Literature - Pulp & Paper Solutions](#)

## Related Products

[SHC125 - Wire and Cable Management, Support Grips, Heavy Duty, Double Eye, Tin-Coated Bronze, 1.25-1.49"](#)  
[SHC100U - Wire and Cable Management, Support Grips, Heavy Duty, Single Eye, Tin-Coated Bronze, 1.00-1.24"](#)  
[SHC075U - Wire and Cable Management, Support Grips, Heavy Duty, Single Eye, Tin-Coated Bronze, 0.75-0.99"](#)  
[SHC200DES - Wire and Cable Management, Support Grips, Heavy Duty, Double Eye, Stainless Steel, 2.00-2.49"](#)  
[SHC300 - Wire and Cable Management, Support Grips, Heavy Duty, Double Eye, Tin-Coated Bronze, 3.00-3.49"](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-SHC200-SPEC-EN | REV 7/2023